

## LM ultra-widefield direct stand adapter

### Application example



<b>Description</b>	<b>LM ultra-widefield direct stand adapter</b> with infinite precision optics for direct mounting on the microscope body, with filter holder M37x0,75
<b>Camera</b>	For digital cameras (DSLR) and mirrorless system cameras (DSLM) with APS-C and fullframe-sensor, C-mount-cameras
<b>Optics</b>	anti-reflection plan achromatic coating infinite widefield optic
<b>Weight / Material</b>	approx. 900 g / CNC milled and turned black anodized aluminium

### Microscope magnification of the adapter solution

Sensor format	0,5"	1"	APS-C	Fullframe
<b>Module1</b>	18x	11x	6x Ultra widefield	4x Ultra widefield
<b>Module 1 + 2</b>	36x	22x	12x	8x widefield

